















| Symbol | Count | Hole Size | Plated | Hole Type |
|-----------|-------|---------------------|--------|-----------|
| □ | 2 | 27.56mil (0.700mm) | PTH | Round |
| B | 3 | 25.00mil (0.635mm) | PTH | Round |
| ✕ | 5 | 47.24mil (1.200mm) | PTH | Round |
| ✖ | 5 | 125.00mil (3.175mm) | PTH | Round |
| ⊠ | 10 | 55.12mil (1.400mm) | PTH | Round |
| ⌘ | 15 | 63.00mil (1.600mm) | PTH | Round |
| ✱ | 62 | 36.00mil (0.914mm) | PTH | Round |
| A | 380 | 12.00mil (0.305mm) | PTH | Round |
| 482 Total | | | | |

