



TGF2978-SM

20 W, 32 V, DC to 12 GHz, GaN RF Transistor


Product Overview

The Qorvo TGF2978-SM is a 20 W (P_{3dB}) discrete GaN on SiC HEMT which operates from DC to 12 GHz and 32 V supply. The device is in an industry standard overmolded package and is ideally suited for avionics, military, marine and weather radar. The device can support pulsed and linear operations.

Lead-free and ROHS compliant.

Evaluation boards are available upon request.

Functional Block Diagram



TGF2978-SMEVB01 Performance


Freq.(GHz)	P_{3dB} (W)	G_{3dB} (dB)	DE_{3dB} (%)
9.0	17.6	6.3	41.2
9.2	17.9	6.7	42.8
9.5	16.8	6.8	41.2
9.8	14.0	6.3	41.1
10.0	12.7	4.8	38.1

Pulse Signal, 100us pulse width, 20% duty cycle
 $V_D = +32\text{ V}$, $I_{DQ} = 140\text{ mA}$, 25°C Base Temperature

TGF2978-SMEVB03 Performance

Freq.(GHz)	P_{3dB} (W)	G_{3dB} (dB)	DE_{3dB} (%)
3.1	18.1	14.9	63.2
3.2	17.7	15.0	62.5
3.3	17.9	14.7	60.4
3.4	18.6	14.3	59.7
3.5	18.9	13.7	58.7

Pulse Signal, 100us pulse width, 20% duty cycle
 $V_D = +32\text{ V}$, $I_{DQ} = 100\text{ mA}$, 25°C Base Temperature



3 x 4mm QFN Package

Key Features

- Frequency Range: DC – 12 GHz
 - Output Power (P_{3dB})¹: 20 W
 - Typical PAE¹: 45%
 - Linear Gain¹: 9.5 dB
 - Operating Voltage: 32 V
 - CW and Pulse capable
- Note 1: @ 9 GHz

Applications

- Military radar
- Commercial radar
 - Avionics
 - Marine
 - Weather

Ordering Information

Part Number	Description
TGF2978-SM	QFN Packaged Part
TGF2978-SMEVB01	9.0 – 10.0 GHz EVB
TGF2978-SMEVB02	2.7 – 3.3 GHz EVB
TGF2978-SMEVB03	3.1 – 3.5 GHz EVB
TGF2978-SMEVB04	4.0 – 5.0 GHz EVB
TGF2978-SMEVB05	5.0 – 6.0 GHz EVB

Absolute Maximum Ratings

Parameter	Rating
Drain to Gate Voltage (V_{DG})	100 V
Gate Voltage Range (V_G)	-7 to +2 V
Drain Current (I_D)	2.4 A
Gate Current (I_G)	-5 to 8.4 mA
Power Dissipation, CW (P_D)	28 W
CW Input Power (P_{IN})	36 dBm
Storage Temperature	-65 to 150°C

Exceeding any one or a combination of the Absolute Maximum Rating conditions may cause permanent damage to the device. Extended application of Absolute Maximum Rating conditions to the device may reduce device reliability.

Note:

1. Pulse (20% Duty Cycle, 100 μ s Width)

Recommended Operating Conditions

Parameter	Min	Typ	Max	Units
Drain Voltage Range (V_D)	-	+32	+40	V
Drain Quiescent Current (I_{DQ})	-	100	-	mA
Gate Voltage, V_G^1	-	-2.7	-	V
Gate Leakage: $V_D = +10$ V, $V_G = -3.7$ V	-5.54	-	-	mA

Electrical specifications are measured at specified test conditions. Specifications are not guaranteed over all recommended operating conditions.

Note:

1. To be adjusted to desired I_{DQ}

Measured Load Pull Performance – Power Tuned¹

Test conditions unless otherwise noted: T = 25°C, Pulse (20% Duty Cycle, 100 μ s Width).

Parameter	Typical Values					Units
	5	6	8	9	10	
Frequency, F	5	6	8	9	10	GHz
Drain Voltage, V_D	32	32	32	32	32	V
Drain Bias Current, I_{DQ}	100	100	100	100	100	mA
Output Power at 3dB compression, P_{3dB}	43.8	43.7	43.4	43.1	42.8	dBm
Power Added Efficiency at 3dB compression, PAE_{3dB}	50.7	50.1	44.6	37.0	35.4	%
Gain at 3dB compression, G_{3dB}	13.4	11.9	8.1	6.5	5.7	dB

Notes:

1. Characteristic Impedance, $Z_0 = 15 \Omega$.

Measured Load Pull Performance – Efficiency Tuned¹

Test conditions unless otherwise noted: T = 25°C, Pulse (20% Duty Cycle, 100 μ s Width).

Parameter	Typical Values					Units
	5	6	8	9	10	
Frequency, F	5	6	8	9	10	GHz
Drain Voltage, V_D	32	32	32	32	32	V
Drain Bias Current, I_{DQ}	100	100	100	100	100	mA
Output Power at 3dB compression, P_{3dB}	42.4	42.6	42.5	42.2	42.4	dBm
Power Added Efficiency at 3dB compression, PAE_{3dB}	60.0	58.0	51.3	45.4	39.8	%
Gain at 3dB compression, G_{3dB}	14.5	12.4	8.8	7.3	6.1	dB

Notes:

1. Characteristic Impedance, $Z_0 = 15 \Omega$.

Thermal and Reliability Information - CW ⁽¹⁾

Parameter	Test Conditions	Value	Units
Thermal Resistance, Peak IR Surface Temperature at Average Power (θ_{JC})	$P_{DISS} = 30.2 \text{ W}$, $T_{baseplate} = 85^\circ\text{C}$	5.9	$^\circ\text{C/W}$
Channel Temperature, T_{CH}		263	$^\circ\text{C}$
Thermal Resistance, Peak IR Surface Temperature at Average Power (θ_{JC})	$P_{DISS} = 25.5 \text{ W}$, $T_{baseplate} = 85^\circ\text{C}$	5.6	$^\circ\text{C/W}$
Channel Temperature, T_{CH}		227	$^\circ\text{C}$
Thermal Resistance, Peak IR Surface Temperature at Average Power (θ_{JC})	$P_{DISS} = 20.2 \text{ W}$, $T_{baseplate} = 85^\circ\text{C}$	5.2	$^\circ\text{C/W}$
Channel Temperature, T_{CH}		191	$^\circ\text{C}$
Thermal Resistance, Peak IR Surface Temperature at Average Power (θ_{JC})	$P_{DISS} = 15.1 \text{ W}$, $T_{baseplate} = 85^\circ\text{C}$	5.0	$^\circ\text{C/W}$
Channel Temperature, T_{CH}		160	$^\circ\text{C}$

Notes:

1. Assumes eutectic attach using 1.5mil thick 80/20 AuSn mounted to a 10 mm x 10 mm x 40 mil CuMo Carrier Plate.
2. Refer to the following document: [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)



Thermal and Reliability Information - Pulsed ⁽¹⁾

Parameter	Test Conditions	Value	Units
Thermal Resistance, Peak IR Surface Temperature at Average Power (θ_{JC})	$P_{DISS} = 30.2 \text{ W}$, $T_{baseplate} = 85^\circ\text{C}$ Pulse Width = 100 μS	2.73	$^\circ\text{C/W}$
Channel Temperature, T_{CH}		Duty Cycle = 10%	167
Thermal Resistance, Peak IR Surface Temperature at Average Power (θ_{JC})	$P_{DISS} = 25.2 \text{ W}$, $T_{baseplate} = 85^\circ\text{C}$ Pulse Width = 100 μS	2.68	$^\circ\text{C/W}$
Channel Temperature, T_{CH}		Duty Cycle = 10%	152

Notes:

1. Assumes eutectic attach using 1.5mil thick 80/20 AuSn mounted to a 10 mm x 10 mm x 40 mil CuMo Carrier Plate.
2. Refer to the following document: [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)


Maximum Channel Temperature



Measured Load Pull Contours

Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (10% Duty Cycle, 100 μs Width).


5GHz, Load-pull



Measured Load Pull Contours

Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (10% Duty Cycle, 100 μs Width).


6GHz, Load-pull



Measured Load Pull Contours

Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (10% Duty Cycle, 100 μs Width).


8GHz, Load-pull



Measured Load Pull Contours

Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (10% Duty Cycle, 100 μs Width).

9GHz, Load-pull




$Z_o = 10\Omega$
3dB Compression Referenced to Peak Gain

Measured Load Pull Contours

Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (10% Duty Cycle, 100 μs Width).

10GHz, Load-pull




$Z_o = 10\Omega$
3dB Compression Referenced to Peak Gain

Measured Load Pull Contours







Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (10% Duty Cycle, 100 μs Width).

12GHz, Load-pull







Typical Measured Performance – Load-Pull Drive-up

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 25\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (20% Duty Cycle, 100 μs Width).







Typical Measured Performance – Load-Pull Drive-up

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 25\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (10% Duty Cycle, 100 μs Width).



S-Parameters Of 9 – 10 GHz EVB

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 140\text{ mA}$, $T = +25^\circ\text{C}$







Notes:

1. The EVB is stable at -40°C and 10:1 VSWR at the output.

Power Driveup Performance Over Temperatures Of 9 – 10 GHz EVB

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 140\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (20% Duty Cycle, 100 μs Width).







Notes:

1. The dissipation power limit is conservative because it is specified at DUT only without accounting for the loss of the output matching network.

Power Driveup Performance Of 9 – 10 GHz EVB

Test Conditions: $V_D = +32V$, $I_{DQ} = 140\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (20% Duty Cycle, 100 μs Width).







Notes:

1. The dissipation power is conservative because it is specified at DUT only without accounting for the loss of the output matching network.





S-Parameters Of 2.7 – 3.3 GHz EVB

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$



Power Driveup Performance Of 2.7 – 3.3 GHz EVB

Test Conditions: $V_D = +32\text{V}$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (20% Duty Cycle, 100 μs Width).







Notes:

1. The dissipation power is conservative because it is specified at DUT only without accounting for the loss of the output matching network.





S-Parameters Of 3.1 – 3.5 GHz EVB

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$



Power Driveup Performance Of 3.1 – 3.5 GHz EVB

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (20% Duty Cycle, 100 μs Width).







Notes:

1. The dissipation power is conservative because it is specified at DUT only without accounting for the loss of the output matching network.





S-Parameters Of 4 – 5 GHz EVB

Test Conditions: $V_D = +32\text{V}$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$



Power Driveup Performance Of 4 – 5 GHz EVB

Test Conditions: $V_D = +32\text{ V}$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (20% Duty Cycle, 100 μs Width).







Notes:

1. The dissipation power is conservative because it is specified at DUT only without accounting for the loss of the output matching network.





S-Parameters Of 5 – 6 GHz EVB

Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$



Power Driveup Performance Of 5 – 6 GHz EVB

Test Conditions: $V_D = +32V$, $I_{DQ} = 100\text{ mA}$, $T = +25^\circ\text{C}$, Pulse (20% Duty Cycle, 100 μs Width).





Notes:

1. The dissipation power is conservative because it is specified at DUT only without accounting for the loss of the output matching network.

9 – 10 GHz Application Circuit - Schematic

Board material is RO4003C 0.008" thickness with 1oz copper cladding. Overall EVB size is 1.5" x 2".





9 – 10 GHz Application Circuit - Bill Of material

Description	Ref. Des.	Manufacturer	Part Number
Capacitor 3.3 pF, 200V, 0402	C1	AVX Corporation	UQCL2A3R3BAT2A\500
Capacitor 0.5 pF, 250V, 0603	C2	Johanson Technology	251R14S0R5AV4T
Capacitor 1.0 uF, 50V, 0805	C6	American Technical Ceramics	C0805C105K5RACTU
Capacitor 2.2 pF, 250V, 0603	C7	American Technical Ceramics	600S1R0AT250XT
Capacitor 5.6 pF, 250V, 0603	C8	American Technical Ceramics	600S5R6BW250XT
Capacitor 100 pF, 250V, 0603	C9	American Technical Ceramics	600S101JT250XT
Capacitor 0.9 pF, 200V, 0402	C12	American Technical Ceramics	600L0R9AT200T
Capacitor 220 uF, 50V, 10 mm	C16	Panasonic Industrial Devices	EEEFK1H221P
Resistor, 47 Ohm, 0603	R1	Rohm Electronics	KTR03EZPF47R0
Resistor, 33.2 Ohm, 0603	R8, R9	Vishay Americas Inc	CRCW060333R2FKTA
Inductor 3.3 nH, 0402	L1	Murata Electronics	LQW15AN3N3B80D
Inductor 1.8 nH, 0402	L2	Coilcraft, Inc.	0402CS-1N8XJEW

2.7 – 3.3 GHz Application Circuit - Schematic

Board material is RO4350B 0.020" thickness with 1oz copper cladding. Overall EVB size is 2.5" x 2".





2.7 – 3.3 GHz Application Circuit - Bill Of material

Description	Ref. Des.	Manufacturer	Part Number
Capacitor 10 pF, 250V, 0603	C1	American Technical Ceramics	600S100JT250XT
Capacitor 1.5 pF, 250V, 0603	C2	American Technical Ceramics	600S1R5AT250X
Capacitor 2.2 pF, 250V, 0603	C4, C12	American Technical Ceramics	600S2R2BT250T
Capacitor 100 pF, 200V, 0603	C5, C8	Capax Technologies	0603G101J201S
Capacitor 0.01 uF, 50V, 0603	C6, C9	Kemet	C0603C103K5RACTU
Capacitor 1 uF, 50V, 1206	C11, C13	TDK Singapore (PTE) LTD	C3216X7R1H105K160AB
Capacitor 47 uF, 80V, 10 mm	C14	Panasonic Industrial Devices	EEETG1K470UP
Resistor, 47 Ohm, 0603	R1	Rohm Electronics	KTR03EZPF47R0
Resistor, 33.2 Ohm, 0603	R5, R6, R8	Vishay Americas Inc	CRCW060333R2FKTA
Resistor, 0 Ohm, 0603	R7	Vishay Americas Inc	CRCW06030000Z0EA
Inductor 5.6 nH, 0603	L1	Coilcraft, Inc.	0603CS-5N6XJEW
Inductor 5.6 nH, 1606	L2	Coilcraft, Inc.	1606-6GLC

3.1 – 3.5 GHz Application Circuit - Schematic

Board material is RO4350B 0.020" thickness with 1oz copper cladding. Overall EVB size is 2.5" x 2".





3.1 – 3.5 GHz Application Circuit - Bill Of material

Description	Ref. Des.	Manufacturer	Part Number
Capacitor 0.7 pF, 250V, 0603	C1	American Technical Ceramics	600S0R7AT250XT
Capacitor 1 pF, 250V, 0603	C2	American Technical Ceramics	600S1R0AT250XT
Capacitor 2.2 pF, 250V, 0603	C3	American Technical Ceramics	600S2R2BT250T
Capacitor 100 pF, 200V, 0603	C4, C9	Capax Technologies	0603G101J201S
Capacitor 0.01 uF, 50V, 0603	C5, C10	Kemet	C0603C103K5RACTU
Capacitor 0.1 uF, 50V, 0603	C6, C11	Kemet	C0603C104J5RACTU
Capacitor 1 uF, 50V, 10 mm	C13	Taiyo Yuden PTE LTD	UMK107AB7105KA
Capacitor 100 uF, 80V, 8 mm	C14	Panasonic Industrial Devices	EEE-1HA101UAP
Resistor, 0 Ohm, 0603	R1	Vishay Americas Inc	CRCW06030000Z0EA
Resistor, 50 Ohm, 0603	R2, R3, R4, R5, R6, R7, R8	Vishay Americas Inc	CRCW06030000Z0EA
Inductor 5.6 nH, 0603	L1	Coilcraft, Inc.	0603CS-5N6XJEW

4 – 5 GHz Application Circuit - Schematic

Board material is RO4350B 0.020" thickness with 1oz copper cladding. Overall EVB size is 1.5" x 2".





4 – 5 GHz Application Circuit - Bill Of material

Description	Ref. Des.	Manufacturer	Part Number
Capacitor 2.4 pF, 250V, 0603	C1	American Technical Ceramics	600S2R4AT250XT
Capacitor 5.6 pF, 250V, 0603	C2	American Technical Ceramics	600S5R6BT250XT
Capacitor 2.2 pF, 250V, 0603	C3	American Technical Ceramics	600S2R2BT250T
Capacitor 0.5 pF, 250V, 0603	C4	Johanson	251R14S0R5AV4T
Capacitor 100 pF, 250V, 0603	C5, C8	American Technical Ceramics	600S101JT250XT
Capacitor 0.1 uF, 50V, 0603	C7	Kemet	C0603C104J5RACTU
Capacitor 1.6 pF, 250V, 0603	C11	American Technical Ceramics	600S1R6BT250XT
Capacitor 1.0 uF, 100V, 0805	C12, C13	TDK Singapore (PTE) LTD	C2012X7S2A105M125AB
Capacitor 33 uF, 80V, 10 mm	C14	Panasonic Industrial Devices	EEE-FK1K330P
Resistor, 2.7 Ohm, 0603	R1	Panasonic Industrial Devices	ERJ-6RQF2R7V
Resistor, 820 Ohm, 0603	R2	KOA Speer Electronics, Inc.	RK73B1JTDD821J
Resistor, 22 Ohm, 0603	R3	Panasonic Industrial Devices	ERJ3GEYJ220V
Resistor, 0 Ohm, 0603	R4	Kamaya, Inc	RMC1/16JPTP
Resistor, 33 Ohm, 0603	R5	KOA Speer Electronics, Inc.	RK73B1JTDD330J
Inductor 3.9 nH, 0603	L1	Coilcraft, Inc.	0603HC-3N9XJRW

5 – 6 GHz Application Circuit - Schematic


Board material is RO4003C 0.008" thickness with 1oz copper cladding. Overall EVB size is 1" x 1".



5 – 6 GHz Application Circuit - Bill Of material

Description	Ref. Des.	Manufacturer	Part Number
Capacitor 0.5 pF, 200V, 0402	C1	American Technical Ceramics	600L0R5AT200T
Capacitor 5.6 pF, 250V, 0603	C2	American Technical Ceramics	600S5R6BT250XT
Capacitor 1.2 pF, 250V, 0603	C3	American Technical Ceramics	600S1R2BT250XT
Capacitor 1.2 pF, 200V, 0402	C4	AVX Corporation	UQCL2A1R2BAT2A\500
Capacitor 100 pF, 250V, 0603	C5, C10	American Technical Ceramics	600S101JT250XT
Capacitor 0.01 uF, 50V, 0603	C6, C9	Kemet	C0603T103K5RALTM
Capacitor 0.1 uF, 50V, 10 mm	C7	Kemet	C0603C104J5RACTU
Resistor, 2.7 Ohm, 0805	R1	Panasonic Industrial Devices	ERJ-6RQF2R7V
Resistor, 820 Ohm, 0603	R2	KOA Speer Electronics, Inc.	RK73B1JTDD821J
Resistor, 10 Ohm, 0603	R3	KOA Speer Electronics, Inc.	RK73B1JTDD100J
Resistor, 820 Ohm, 0603	R2	KOA Speer Electronics, Inc.	RK73B1JTDD821J
Resistor, 0 Ohm, 0603	R4	Kamaya, Inc	RMC1/16JPTP
Resistor, 33 Ohm, 0603	R5, R6, R7, R9, R10	KOA Speer Electronics, Inc.	RK73B1JTDD330J
Inductor 8.2 nH, 0603	L1	Murata Electronics	LQP18MN8N2C02D

Mechanical Information^{1, 2, 3}




Note:

1. All dimensions are in millimeters.
2. Unless otherwise noted, all dimension tolerances are ± 0.127 mm.
3. This package is lead-free/RoHS-compliant. The plating material on the leads is NiPdAu. It is compatible with both lead-free (maximum 260°C reflow temperature) and tin-lead (maximum 245°C reflow temperature) soldering process.


Pin Configuration and Description¹

Note 1: The TGF2978-SM will be marked with the “2978” designator and a lot code marked below the part designator. The “YY” represents the last two digits of the calendar year the part was manufactured, the “WW” is the work week of the assembly lot start, the MZZZ” is the production lot number.



Pin	Symbol	Description
12 - 15	V_D / RF OUT	Drain voltage / RF Output to be matched to 50 ohms; see EVB Layout on page 19 as an example.
3 - 4	V_G / RF IN	Gate voltage / RF Input to be matched to 50 ohms; see EVB Layout on page 19 as an example.
1 - 2, 5 - 11, 16 - 20	N/C	Not connected
Back side	Source	Source connected to ground

Recommended Soldering Temperature Profile



Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	Class 1A (250 V)	ANSI/ESDA/JEDEC Standard JS-001
ESD – Charged Device Model (CDM)	Class C6 (2000 V)	ANSI/ESDA/JEDEC Standard JS-002
MSL – Moisture Sensitivity Level	N/A	IPC/JEDEC Standard J-STD-020

Not HAST compliant.



Solderability

Compatible with both lead-free (260°C max. reflow temp.) and tin/lead (245°C max. reflow temp.) soldering processes.

Solder profiles available upon request.

Contact plating: NiPdAu

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- PFOS Free
- SVHC Free



Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2026 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.